



HearPlus 317ci

amplified corded phone for the hearing impaired



Doro Audio Plus



superior ergonomics



hearing aid compatible

Doro HearPlus 317ci combines excellent ergonomics with superb visual aids, improved hearing aid compatibility and enhanced sound adjustments for people with severely impaired hearing. It is also very easy to understand and to use.





volume control



strobe light

HearPlus 317ci

Colour: white / dark grey

Ergonomics		Calling/Talking	
Light weight handset (gram)	220	Speakerphone	•
Heavy stable base, weight (gram)	860	Extra large, high contrast display	•
Easy to place handset	•	Redial memory	5
Easy grip comfortable handset	•	Pre dialling	•
High contrast keys with low reflective finish	•	One touch memories	4
Concave keys	•	Easy operation slide volume setting	•
Easy clean surfaces	•	Boost mode	•
Low profile front for easy operation	•	Call timer	•
Hearing		Off hook warning lamp	•
Doro Audio +	•	Handset LCD display	
Receiving minimum level (dB RLR)	0	Display with zoom function	•
Receiving minimum level (dB(A))	88	Extra large display with high contrast	•
Receiving maximum level (dB RLR)	-35	Display size (mm)	108*23
Receiving maximum level (dB(A))	123	Graphical dot matrix	•
Sending level adjustment	+/-6	Colour display	Black on white / White on Black
Maximum receiver output level (dB(A))	125	Lines / Characters	2/21
Tone adjustment at 250Hz (dB)	6	Backlit display	•
Tone adjustment at 4KHz (dB)	12	Big display font	•
HAC level sensitivity at 1KHz (dB-A/M)	-23	Clock	•
HAC linearity +/-1dB	•	Caller ID	
HAC frequency response permissible range	•	Caller ID on hook*	•
HAC frequency response preferred range	•	Caller ID off hook (call waiting)**	•
Maximum ringer volume (dB(A) at 1 meter)	91	Name display from phone book	•
Lowest ringer centre frequency (Hz)	700	Name display from the network**	•
Highest ringer centre frequency (Hz)	2000	Date & time stamp - network**	•
Ringer		Date & time stamp - internal clock	•
Monophonic ring tones	9	Caller ID memory	10
Ringer volume settings except off	3		
Ringer off setting	•		
Ringer strobe	•		
Vibration alert outlet	•		

* Depending on network support and subscription
 ** Country depending

Doro Audio+ for improved hearing aid compatibility and enhanced sound amplification including loud handset volume with special boost function, receiver tone adjustment, loud ringer with multiple frequency settings, strobe ringer and compliance with HAC standards at preferred levels.

