



MemoryPlus 319ph

amplified photo phone



comfortable, ergonomically designed grip



easy to use – just lift and press



hearing aid compatible



care electronics

doro® 



Speed dial buttons with photos

Sliding volume control

Doro MemoryPlus 319ph is especially helpful for people with limited dexterity or cognitive impairments. The ergonomically designed keypad, photo buttons, handset and sure slide cradle make it easy to stay in touch with the people you rely on.

MemoryPlus 319ph

Colour: white/dark grey

| Calling/talking | | Hearing | |
|--|-------|--|------|
| Redial memory | 1 | Receiving min level (dB RLR) | -5 |
| One-touch photo memories | 4 | Receiving min level (dB(A)) | 93 |
| Handset volume settings | Slide | Receiving maximum level (dB RLR) | -18 |
| Ringer | | Receiving maximum level (dB(A)) | 106 |
| Monophonic ring tones | 9 | Maximum receiver output level (dB(A)) | 125 |
| Ringer volume settings except off | 3 | Tone adjustment at 250Hz (dB) | 6 |
| Ringer lamp | • | Tone adjustment at 4KHz (dB) | 12 |
| Ringer off setting | • | HAC level sensitivity at 1KHz (dB-A/M) | -23 |
| Ergonomics | | HAC linearity +/-1dB | • |
| High contrast, concave keys with low reflective finish | • | HAC frequency response preferred range | • |
| Robust base unit for greater stability | • | Maximum ringer volume (dB(A) at 1 meter) | 85 |
| Comfortable handset | • | Lowest ringer centre frequency (Hz) | 90 |
| Easy to clean surfaces | • | Highest ringer centre frequency (Hz) | 2000 |
| Low profile front to reduce strain | • | | |

